Bona Power Drive®

Sanding



Technical data sheet

The Bona Power Drive[®] is a powerful and flexible machine that can be equipped with many different drive plates for a wide variety of floor preparation. With its powerful 1.9 kW, 2.6 HP motor and sturdy construction, it runs smooth and stays cool even under a heavy load. The Bona Power Drive provides powerful rotary sanding to bare wood and reduces the time needed to edge dramatically. The Bona Power Drive delivers an amazingly fine and smooth sanding result and minimizes the risk of drum marks or chatter.

- Powerful, single phase motor
- Forced driven geared drive plate
- Four individually geared grinding pads
- Easy and ergonomic operation
- Large wheels for easy transportation
- DCS compatible for dust free sanding
- Multiple drive plate capability

Technical data

- Motor: 2. HP Heavy Duty, Dual Capacitor 240 Volt/163 RPM, 11.5 AMP, 60HZ Gear Box: 10-1, all-steel, permanently sealed & lubricated
- Switch: Dual Control Safety Lock Trigger Mechanism
- Machine Weight: 111 Lbs.
- Pad Driver Size: one 16" drive plate or four 6" disc Illumination: Two long-life, high-output LED Bulbs Recommended fuses 15A

Order Information

 Item#
 Lbs.

 AMO310002.5
 111

 Power Drive Plate
 8.9

 ASO312540
 Standard 16" Drive Plate

 Standard 16" Drive Plate
 7







Bona Sanding Sequences for a Perfect Surface







Bona Diamond



Natural, Stained or Oiled Floor			or (for any floor requi	(for any floor requiring the least amount of scratches)	
Coarse Sanding	Medium Sanding		Fine Sanding		
40 to 50-grit	⇒ 60 to 80-grit ⇒	60 to 80-grit =	100 to 120-grit 🖨	80 to 120-grif	
Bona Green Belt or Bona Green Disc	Bona Blue Disc on Bona Power Drive	Bona Blue Disc on Edger	Bona Black Disc on Bona Power Drive	Bona Diamond Disc with Bona MultiDisc	
OPTION: 2x weights	OPTION: 1x weight		OPTION:	OPTION:	
plus Steel Plates on Bona Power Drive	plus Steel Plates on Bona Power Drive		Bona Steel Plates on Power Drive	Bona Steel Plates	

Wire-Brushed Floor

Coarse Sanding

40 to 50-grit

Bona Breen Belt

Bona Breen Bent

Bona Breen

Bona Breen Bent

Bona Breen

"When a softer brushing effect is desired, use the Tynex Brush after wire-brushing